# Base Plates • suitable on pallets DIN 55 201

1000.800



# **Product Description**

### **Material**


· Steel, hardened, ground

### More information

# Notes

Special types on request.

# Drawing



 $<sup>^{\</sup>star}$  These tolerances are valid only for optional exterior stop type. Slot spacing 40 ±0,01.


### **Order information**

System	Dimensions									у	Number	T T	Art. No.
	а	b <sub>1</sub>	b <sub>2</sub>	b <sub>3</sub>	С	d	I <sub>1</sub>	l <sub>2</sub>	l <sub>3</sub>		of T-slots		
	[mm]									[mm]		[kg]	
V40	100	320	100	40	40	20	320	100	40	10	7 x 7	28	1000.800





Halder France SAS www.halder.fr

# **Application example**









# Compliance

### **RoHS** compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

### Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

### Does not contain Proposition 65 substances

No Proposition 65 substances included. https://www.P65Warnings.ca.gov/

### **Free from Conflict Minerals**

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.



Halder France SAS www.halder.fr Page 4 of 4
Published on: 4.2.2024