

SIMPLEX soft-face mallets • Plastic; with reinforced cast iron housing and fibre-glass handle EH 3706.



Product Description

The SIMPLEX series 3706 is equipped with the plastic insert on either side. This red insert (series 3206) is hard and also oil and grease resistant. The black, reinforced cast iron housing provides for greater stability thanks to the enlarged wall thicknesses and struts. The increase in weight ensures greater impact force. Extremely rugged and durable, the fibre glass handle offers exceptional break resistance. It is shaped ergonomically and includes a non-slip handle. It possesses a smooth surface and is inorganic (non-sensitive to moisture). In line with the smart SIMPLEX principle, all components are replaceable and can be retrofitted. This translates to savings in both money and resources. This version is available in sizes ranging from D30mm to D60mm.

Product features:

- SIMPLEX soft-face mallet with plastic inserts (red, hard, oil and grease resistant) on both sides.
- Reinforced cast iron housing with great stability boosts impact force by adding weight.
- Exceptionally rugged and durable fibre glass handle with non-slip grip, inorganic (non-sensitive to moisture).
- All parts can be replaced / retrofitted, resulting in great savings in cost and resources.
- Available in sizes of D30mm to D60mm.

Application Areas

Versatile use, assembly and repair work, maintenance work, sheet-metal forming, prefabricated house construction, carpenter's work, scaffold construction, tent construction

Material

Handle

- Fibreglass with rubber grip





Inserts

- Plastic, red
- hard
- Oil and grease resistant

Housing

- Reinforced cast iron, black

Order information

Ø	Dimensions			Length x Width x Height [in]	 [oz]	GTIN	proficl@ss 5.0	ecl@ss 10.1	Art. No.
									
1.18	3.54	11.81		11.81 x 3.54 x 1.34	15.87	4030618303459	AAA905c002	21-04-09-16	3706.030
1.57	4.53	12.80		12.80 x 4.53 x 1.57	30.69	4030618303466	AAA905c002	21-04-09-16	3706.040
1.97	5.31	13.19		13.19 x 5.31 x 1.97	43.39	4030618303473	AAA905c002	21-04-09-16	3706.050
2.36	5.91	16.14		16.14 x 5.91 x 2.68	63.49	4030618303480	AAA905c002	21-04-09-16	3706.060

Compliance

RoHS compliant

Compliant according to Directive 2011/65/EU and Directive 2015/863.

Does not contain SVHC substances

No SVHC substances with more than 0.1% w/w contained - SVHC list [REACH] as of 23.01.2024.

Does not contain Proposition 65 substances

No Proposition 65 substances included.

<https://www.P65Warnings.ca.gov/>

Free from Conflict Minerals

This product does not contain any substances designated as "conflict minerals" such as tantalum, tin, gold or tungsten from the Democratic Republic of Congo or adjacent countries.