Thrust Screws • with brass pad
EH 22760.



Product Description

Thrust screws can be used for a gentle clamping or pressing of thread spindles, axes, shafts and surface treated parts.

Material

Pad
- Brass


Screw
- Heat-treated steel, 1200 ±100 N/mm^2
- Stainless steel 1.4305

More information

Further products

- Thrust Screws, with plastic pad

Drawing




Order information

Dimensions				WS			Art. No.
d_1	l_1	l_2	d_2		max.		
[mm]				[mm]	[°C]	[g]	
Heat-treated steel							
M 3	**5.0**	1.0	1.5	1.5	250	0.1	22760.0032
M 3	**7.5**	1.0	1.5	1.5	250	0.2	22760.0034
M 3	**10.0**	1.0	1.5	1.5	250	0.3	22760.0036
M 4	**5.0**	1.0	2.5	2.0	250	0.3	22760.0040
M 4	**6.5**	1.2	2.5	2.0	250	0.3	22760.0042
M 4	**10.5**	1.2	2.5	2.0	250	0.6	22760.0044
M 4	**16.5**	1.2	2.5	2.0	250	1.0	22760.0046
M 5	**6.0**	1.0	3.0	2.5	250	0.5	22760.0050
M 5	**8.5**	1.3	3.0	2.5	250	0.7	22760.0052
M 5	**12.5**	1.3	3.0	2.5	250	1.2	22760.0054
M 5	**20.5**	1.3	3.0	2.5	250	2.1	22760.0056
M 6	**6.0**	1.0	4.0	3.0	250	0.7	22760.0060
M 6	**11.5**	1.9	4.0	3.0	250	1.5	22760.0062
M 6	**17.5**	1.9	4.0	3.0	250	2.5	22760.0064
M 6	**26.5**	1.9	4.0	3.0	250	4.0	22760.0066
M 8	**8.0**	1.4	5.5	4.0	250	1.7	22760.0080
M 8	**12.0**	2.5	5.5	4.0	250	2.9	22760.0082
M 8	**22.0**	2.5	5.5	4.0	250	5.7	22760.0086
M 8	**32.0**	2.5	5.5	4.0	250	8.7	22760.0088
M10	**10.0**	1.5	7.0	5.0	250	3.4	22760.0100
M10	**14.0**	2.7	7.0	5.0	250	5.4	22760.0102
M10	**18.0**	2.7	7.0	5.0	250	6.7	22760.0104
M10	**27.0**	2.7	7.0	5.0	250	11.0	22760.0106
M10	**37.0**	2.7	7.0	5.0	250	16.0	22760.0108
M12	**12.0**	1.5	8.5	6.0	250	6.4	22760.0120

Dimensions				WS	max.		Art. No.
d_1	l_1	l_2	d_2				
[mm]				[mm]	[°C]	[g]	
M12	**18.5**	3.4	8.5	6.0	250	10.0	22760.0122
M12	**22.5**	3.4	8.5	6.0	250	12.0	22760.0124
M12	**32.5**	3.4	8.5	6.0	250	19.0	22760.0126
M12	**42.5**	3.4	8.5	6.0	250	26.0	22760.0128
Stainless steel							
M 3	**5.0**	1.0	1.5	1.5	250	0.1	22760.0432
M 3	**7.5**	1.0	1.5	1.5	250	0.2	22760.0434
M 3	**10.0**	1.0	1.5	1.5	250	0.3	22760.0436
M 4	**6.5**	1.2	2.5	2.0	250	0.3	22760.0442
M 4	**10.5**	1.2	2.5	2.0	250	0.6	22760.0444
M 4	**16.5**	1.2	2.5	2.0	250	1.0	22760.0446
M 5	**8.5**	1.3	3.0	2.5	250	0.7	22760.0452
M 5	**12.5**	1.3	3.0	2.5	250	1.2	22760.0454
M 5	**20.5**	1.3	3.0	2.5	250	2.1	22760.0456
M 6	**11.5**	1.9	4.0	3.0	250	1.5	22760.0462
M 6	**17.5**	1.9	4.0	3.0	250	2.5	22760.0464
M 6	**26.5**	1.9	4.0	3.0	250	4.0	22760.0466
M 8	**12.0**	2.5	5.5	4.0	250	2.9	22760.0482
M 8	**22.0**	2.5	5.5	4.0	250	5.7	22760.0486
M 8	**32.0**	2.5	5.5	4.0	250	8.7	22760.0488
M10	**14.0**	2.7	7.0	5.0	250	5.4	22760.0502
M10	**18.0**	2.7	7.0	5.0	250	6.7	22760.0504
M10	**27.0**	2.7	7.0	5.0	250	11.0	22760.0506
M10	**37.0**	2.7	7.0	5.0	250	16.0	22760.0508
M12	**18.5**	3.4	8.5	6.0	250	10.0	22760.0522
M12	**22.5**	3.4	8.5	6.0	250	12.0	22760.0524
M12	**32.5**	3.4	8.5	6.0	250	19.0	22760.0526
M12	**42.5**	3.4	8.5	6.0	250	26.0	22760.0528

Application example



Compliance

For detailed compliance information please select the desired article number.